



Bronze Clamp with Copper Strap, Cable to Water Pipe/Rebar

By Burndy
Catalog # C11CSLH12



Cast Bronze Ground Clamp w/Cu Strap, 1/2"-1" Water Pipe, #4-#6 Rebar(Main), 1/2" Hub, 2/0-#10 Ground, Zinc Plated H/W

Features

- For grounding rigid conduit systems, straps helps protect conduit system from water system vibrations
- Zinc-plated screw, Strap ETP Copper

- 2/0 AWG

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Pipe EMT Size	1/2 in 3/4 in 1 in
Conductor - Copper Str Size Range	10 AWG - 2/0 AWG
Conductor - Copper Str Size	10 AWG 9 AWG 8 AWG 7 AWG 6 AWG 5 AWG 4 AWG 3 AWG 2 AWG 1 AWG 1/0 AWG

Dimensions

Dimension - Pad Width inch	1.06 in
Package Height	0.000 in
Dimension - Height mm	44.5 mm
Length	6.18 in
Dimension - Height inch	1.75 in
Package Weight	0.000 lb.
Dimension - Width mm	30 mm
Dimension - Width inch	1.18 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	216 mm
Width	0.66 in
Dimension - D inch	6.12 in
Dimension - Length Overall inch	8.50 in

General

Plated	N
Material - Hardware	Zinc Plated Steel
UPC	781810358658
Material	Bronze Alloy
Plating Type	Zinc
UPC 12 Digit	781810358658
UPC 14 Digit GTIN	00781810358658

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2800
Carton Quantity	35

Product Assets

[Catalog \[English\]](#)