

C11JA, Cast Bronze Clamp, Armored Cable to Water Pipe

By Burndy
Catalog # [C11JA](#)

Cast Bronze Clamp, Armored Cable to Water Pipe, 10 AWG - 6 AWG, 1/2" - 1" Water Pipe

Features

- Zinc plated screws
- Pressure bar grips armor or outer cable insulation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG
Conductor - Pipe EMT Size Range	1/2in -1 in
Conductor - Pipe EMT Size	• 3/8 in • 1/2 in • 3/4 in • 1 in
Conductor - Armored Cable Size	Y
Conductor - Copper Solid Size Range	10 AWG-6 AWG
Conductor Type	• Pipe EMT-Size • CU C Solid-Size



Conductor - Copper Str Size Range	• CU C Str-Size 8 AWG - 6 AWG
Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	35.1 mm
Dimension - Height inch	1.38 in
Package Weight	0.000 lb.
Dimension - Width mm	36 mm
Dimension - Width inch	1.41 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	77 mm
Dimension - Length Overall inch	3.05 in

General

Plated	N
Material - Hardware	Zinc Plated Steel
UPC	781810142110
Material	Bronze Alloy
Plating Type	Unplated
UPC 12 Digit	781810142110
UPC 14 Digit GTIN	00781810142110

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3500
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)