

C11JPT, Cast Bronze Clamp, Cable to Water Pipe

By Burndy
Catalog # [C11JPT](#)

Cast Bronze Clamp, Cable to Water Pipe, 10 AWG - 6 AWG, 1/2" - 1" Water Pipe, 1/2" Hub



Features

- Pressure bar type conduit hub adjusts for 1/2", 3/4" EMT, or 1/2" rigid conduit
- Supplied with zinc plated hardware

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG
Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Pipe EMT Size	• 1/2 in • 3/4 in • 1 in
Conductor - Armored Cable Size	N
Conductor - Copper Solid Size Range	10 AWG-6 AWG
Conductor Type	• Pipe EMT-Size • CU C Solid-Size

Conductor - Copper Str Size Range	8 AWG - 6 AWG
Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	52.6 mm
Dimension - Height inch	2.07 in
Package Weight	0.000 lb.
Dimension - Width mm	54 mm
Dimension - Width inch	2.13 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.19 in

General

Plated	N
Material - Hardware	Zinc Plated Steel
UPC	781810142257
Material	Bronze Alloy
Plating Type	Unplated
UPC 12 Digit	781810142257
UPC 14 Digit GTIN	00781810142257

Logistics

Minimum Pack Quantity	30
Pallet Quantity	3600
Carton Quantity	30

Product Assets

[Catalog \[English\]](#)