



C11K17D, Cast Bronze Ground Clamp with Lay-in Feature, for Water Pipe, Rebar, Ground Rod, to Tap Conductor

By Burndy  
Catalog # C11K17D

Cast Bronze Ground Clamp w/Lay-in Feature, 1/2"-1" Water Pipe, #4-#6 Rebar, 3/8"-1" Ground Rod(Main), #10 Sol-#2 Str Ground, Silicon Bronze H/W

Features

- Lay-In Feature
- Connects Grounding Conductor to Water Pipe, Copper Tube, Ground Rod or Rebar
- Open face design allows for a fast lay-in on the tap conductor without need for cutting
- Reverse bottom clamp for smaller size, rebar or rod

Application

For Connecting Grounding Conductor To Water Pipe, Copper Tube, Ground Rod Or Rebar And Direct Burial

Specifications

|                                         |                      |
|-----------------------------------------|----------------------|
| Certification - UL Recognized           | No                   |
| Buy American Compliant                  | Contact Manufacturer |
| Certification - cULus                   | No                   |
| Buy America(n) Qualified                | Contact Manufacturer |
| Industry Standard(s)                    | UL467                |
| Certification - ETL                     | No                   |
| Standards - Industry Standards Met      | UL467                |
| Standards - RoHS Compliance             | CM                   |
| Status                                  |                      |
| Certification - UL Listed Direct Burial | Yes                  |
| UL Listed                               | No                   |
| Certification - CSA Approved            | No                   |

Conductor

|                                 |                                                                                                                                          |
|---------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Rebar Size          | <ul style="list-style-type: none"><li>• 4</li><li>• 5</li><li>• 6</li></ul>                                                              |
| Conductor - Rebar Size Range    | 4 -6                                                                                                                                     |
| Conductor - Pipe EMT Size Range | 1/2 in-1 in                                                                                                                              |
| Conductor - Pipe EMT Size       | <ul style="list-style-type: none"><li>• 1/2 in</li><li>• 3/4 in</li><li>• 1 in</li></ul>                                                 |
| Conductor - Rod Size Range      | 3/8 in-1 in                                                                                                                              |
| Conductor - Copper Str Size     | <ul style="list-style-type: none"><li>• 10 AWG</li><li>• 9 AWG</li><li>• 8 AWG</li><li>• 7 AWG</li><li>• 6 AWG</li><li>• 5 AWG</li></ul> |



|                                   |                                                                                                                                                                                             |
|-----------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Rod Size              | <ul style="list-style-type: none"><li>• 4 AWG</li><li>• 3 AWG</li><li>• 2 AWG</li><li>• 3/8 in</li><li>• 1/2 in</li><li>• 5/8 in</li><li>• 3/4 in</li><li>• 7/8 in</li><li>• 1 in</li></ul> |
| Conductor - Copper Str Size Range | 10 AWG - 2 AWG                                                                                                                                                                              |

Dimensions

|                                 |                             |
|---------------------------------|-----------------------------|
| Package Height                  | 0.000 in                    |
| Dimension - Height mm           | 41.7 mm                     |
| Dimension - Height inch         | 1.64 in                     |
| Package Weight                  | 0.000 lb.                   |
| Package Length                  | 0.000 in                    |
| Package Width                   | 0.000 in                    |
| Dimension - L Length Overall mm | 58 mm                       |
| Width                           | 2.28 in                     |
| Length                          | 1.39 in                     |
| Dimension - Width mm            | 17 mm                       |
| Dimension - Width inch          | 0.66 in                     |
| Height                          | 0.66 in                     |
| Dimension - Length Overall inch | 2.28 in                     |
| Dimensions                      | 1.39 in x 2.28 in x 0.66 in |

General

|                                       |                                                                                                                                                  |
|---------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Family                        | Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Ground Rod/Pipe/Tube (GAR/GD/GK)>LC Water Pipe Ground Clamps |
| Material - Hardware Plated            | DURIUM™ Silicon Bronze No                                                                                                                        |
| Sub Brand                             | CLAMP                                                                                                                                            |
| Product Type                          | Mechanical                                                                                                                                       |
| UPC                                   | 781810358634                                                                                                                                     |
| Type                                  | Ground Clamp                                                                                                                                     |
| Construction Material - Main Material | Cast Bronze Body Copper                                                                                                                          |
| Plating Type                          | Unplated                                                                                                                                         |
| UPC 12 Digit                          | 781810358634                                                                                                                                     |

UPC 14 Digit GTIN00781810358634

Carton Quantity100

Logistics

Minimum Pack Quantity1

Pallet Quantity6000

Product Assets

[Catalog \[English\]](#)

