

C11LH3, Cast Bronze Clamp, Cable to Water Pipe

By Burndy
Catalog # [C11LH3](#)

Cast Bronze Clamp, Cable to Water Pipe, 3/0 AWG - 10 AWG, 1/2" - 1"
Water Pipe, 1" hub

Features

- Cast bronze clamps for conduit
- Continuity from rigid conduit systems to ground provided by cast bronze threaded conduit hub
- Zinc plated screws

Application

For Grounding Rigid Conduit Systems

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	NC
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Pipe EMT Size	• 1/2 in • 3/4 in • 1 in
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG



Conductor - Armored Cable Size	• 3/0 AWG N
Conductor - Copper Str Size Range	10 AWG - 3/0 AWG

Dimensions

Dimension - Pad Width inch	1.19 in
Package Height	0.000 in
Dimension - Height mm	68.3 mm
Dimension - Height inch	2.69 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	73 mm
Dimension - Width mm	29 mm
Dimension - Width inch	1.13 in
Dimension - Length Overall inch	2.86 in

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Ground Rod/Pipe/Tube (GAR/GD/GK)>LC Water Pipe Ground Clamps
Material - Hardware	Zinc Plated Steel
Plated	No
Sub Brand	CONDUIT
Product Type	Mechanical
UPC	781810142165
Type	Ground Clamp
Material	Bronze Alloy
Plating Type	Unplated
UPC 12 Digit	781810142165
UPC 14 Digit GTIN	00781810142165

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)