

C22JPT, Cast Bronze Clamp, Cable to Water Pipe

By Burndy
Catalog # [C22JPT](#)

Cast Bronze Clamp, Cable to Water Pipe, 10 AWG - 6 AWG, 1-1/4" - 2" Water Pipe, 1/2" Hub



Features

- Cast bronze clamp for conduit
- Pressure bar type conduit hub adjusts for 1/2", 3/4" EMT, or 1/2" rigid conduit
- Supplied with zinc plated hardware

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG
Conductor - Pipe EMT Size Range	1 1/4 in-2 in
Conductor - Pipe EMT Size	• 1 1/4 in • 1 1/2 in • 2 in
Conductor - Armored Cable Size	N
Conductor - Copper Solid Size Range	10 AWG-6 AWG
Conductor Type	• Pipe EMT-Size

Conductor - Copper Str Size Range

Conductor - Copper Str Size

- CU C Solid-Size 8 AWG - 6 AWG

- 8 AWG
- 7 AWG
- 6 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	68.6 mm
Dimension - Height inch	2.70 in
Package Weight	0.000 lb.
Dimension - Width mm	54 mm
Dimension - Width inch	2.13 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	97 mm
Dimension - Length Overall inch	3.83 in

General

Plated	N
Material - Hardware	Zinc Plated Steel
UPC	781810142264
Material	Bronze Alloy
Plating Type	Unplated
UPC 12 Digit	781810142264
UPC 14 Digit GTIN	00781810142264

Logistics

Minimum Pack Quantity	25
Pallet Quantity	1
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)