

C22LH1, Cast Bronze Clamp, Cable to Water Pipe

By Burndy
Catalog # [C22LH1](#)

Cast Bronze Clamp, Cable to Water Pipe, 10 AWG -6 AWG, 1-1/4" - 2" Water Pipe, 1/2" hub



Features

- Cast bronze clamp for conduit for grounding rigid conduit systems
- Continuity from rigid conduit systems to ground provided by cast bronze threaded conduit hub
- Zinc plated screws supplied
- UL467 Listed for the US and Canadian Markets

- 9 AWG
- 8 AWG
- 7 AWG
- 6 AWG

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	10 AWG
Conductor - Pipe EMT Size Range	1 1/4 in-2 in
Conductor - Pipe EMT Size	• 1 1/4 in • 1 1/2 in • 2 in
Conductor - Armored Cable Size	N
Conductor - Copper Solid Size Range	10 AWG
Conductor - Copper Str Size Range	10 AWG - 6 AWG
Conductor - Copper Str Size	• 10 AWG

Dimensions

Dimension - Pad Width inch	1.34 in
Package Height	0.000 in
Dimension - Height mm	73.2 mm
Dimension - Height inch	2.88 in
Package Weight	0.000 lb.
Dimension - Width mm	18 mm
Dimension - Width inch	0.69 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	89 mm
Dimension - Length Overall inch	3.50 in

General

Plated	N
Material - Hardware	Zinc Plated Steel
UPC	781810142172
Material	Bronze Alloy
Plating Type	Unplated
UPC 12 Digit	781810142172
UPC 14 Digit GTIN	00781810142172

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3000
Carton Quantity	30

Product Assets

[Catalog \[English\]](#)