



C2Y4/OL18D58CG1 Rope Lay Braid

By Burndy
Catalog # C2Y4/OL18D58CG1

Rope Lay Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Package Height	0.000 in
Length	18.58 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	472 mm
Height	0.43 in
Width	1.19 in
Dimension - Length Overall inch	18.58 in
Dimensions	18.58 in x 1.19 in x 0.43 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
UPC	781810460108
Material	Copper
UPC 12 Digit	781810460108
UPC 14 Digit GTIN	00781810460108

Logistics

Minimum Pack Quantity	60
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)