



C4JA, Cast Bronze Clamp, Armored Cable to Water Pipe

By Burndy
Catalog # [C4JA](#)

Cast Bronze Clamp, Armored Cable to Water Pipe, 10 AWG - 6 AWG, 2-1/2" - 4" Water Pipe

Features

- Cast bronze clamp for armored cable to water pipe
- Pressure bar grips armor or outer cable insulation
- Supplied with zinc plated screws
- UL467 Listed for the US and Canadian markets

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG
Conductor - Pipe EMT Size Range	2 1/2 in-4 in
Conductor - Pipe EMT Size	• 2 1/2 in • 3 in • 3 1/2 in • 4 in
Conductor - Armored Cable Size	Y
Conductor - Copper Solid Size Range	10 AWG-6 AWG
Conductor Type	• Pipe EMT-Size



Conductor - Copper Str Size Range	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size	8 AWG - 6 AWG
	• 8 AWG • 7 AWG • 6 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	109 mm
Dimension - Height inch	4.29 in
Package Weight	0.000 lb.
Dimension - Width mm	36 mm
Dimension - Width inch	1.41 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	128 mm
Dimension - Length Overall inch	5.01 in

General

Plated	N
Material - Hardware	Zinc Plated Steel
UPC	781810142134
Material	Bronze Alloy
Plating Type	Unplated
UPC 12 Digit	781810142134
UPC 14 Digit GTIN	00781810142134

Logistics

Minimum Pack Quantity	12
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)