

C4JPT, Cast Bronze Clamp, Cable to Water Pipe

By Burndy
Catalog # [C4JPT](#)

Cast Bronze Clamp, Cable to Water Pipe, 10 AWG - 6 AWG, 2-1/2" - 4" Water Pipe, 1/2" Hub

Features

- Cast bronze clamp for conduit
- Pressure bar type conduit hub adjusts for 1/2", 3/4" EMT, or 1/2" rigid conduit
- Supplied with zinc plated hardware
- UL467 Listed for the US and Canadian markets

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG
Conductor - Pipe EMT Size Range	2 1/2 in-4 in
Conductor - Pipe EMT Size	• 2 1/2 in • 3 in • 3 1/2 in • 4 in
Conductor - Armored Cable Size	N
Conductor - Copper Solid Size Range	10 AWG-6 AWG



Conductor Type	• Pipe EMT-Size • CU C Solid-Size
Conductor - Copper Str Size Range	8 AWG - 6 AWG
Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	111.5 mm
Dimension - Height inch	4.39 in
Package Weight	0.000 lb.
Dimension - Width mm	54 mm
Dimension - Width inch	2.13 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	131 mm
Dimension - Length Overall inch	5.15 in

General

Plated	N
Material - Hardware	Zinc Plated Steel
UPC	781810142271
Material	Bronze Alloy
Plating Type	Unplated
UPC 12 Digit	781810142271
UPC 14 Digit GTIN	00781810142271

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)