

C4LH1, Cast Bronze Clamp, Cable to Water Pipe

By Burndy
Catalog # [C4LH1](#)

Cast Bronze Clamp, Cable to Water Pipe, 10 AWG -6 AWG, 2-1/2" - 4" Water Pipe, 1/2" hub



Features

- Cast bronze clamp for grounding rigid conduit systems
- Continuity from rigid conduit systems to ground provided by cast bronze threaded conduit hub
- Supplied with zinc plated screws
- UL467 Listed for the US and Canadian markets

- 9 AWG
- 8 AWG
- 7 AWG
- 6 AWG

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	10 AWG
Conductor - Pipe EMT Size Range	2 1/2 in-4 in
Conductor - Pipe EMT Size	• 2 1/2 in • 3 in • 3 1/2 in • 4 in
Conductor - Armored Cable Size	N
Conductor - Copper Solid Size Range	10 AWG
Conductor - Copper Str Size Range	10 AWG - 6 AWG
Conductor - Copper Str Size	• 10 AWG

Dimensions

Dimension - Pad Width inch	2.44 in
Package Height	0.000 in
Dimension - Height mm	115.8 mm
Dimension - Height inch	4.56 in
Package Weight	0.000 lb.
Dimension - Width mm	18 mm
Dimension - Width inch	0.69 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	122 mm
Dimension - Length Overall inch	4.82 in

General

Plated	N
Material - Hardware	Zinc Plated Steel
UPC	781810142219
Material	Bronze Alloy
Plating Type	Unplated
UPC 12 Digit	781810142219
UPC 14 Digit GTIN	00781810142219

Logistics

Minimum Pack Quantity	30
Pallet Quantity	1080
Carton Quantity	30

Product Assets

[Catalog \[English\]](#)