

C4LH3, Cast Bronze Clamp, Cable to Water Pipe

By Burndy
Catalog # [C4LH3](#)

Cast Bronze Clamp,Cable to Water Pipe, 3/0 AWG - 10 AWG, 2-1/2" - 4" Water Pipe, 1" hub



Features

- Cast bronze clamp for grounding rigid conduit systems
- Continuity from rigid conduit systems to ground provided by cast bronze threaded conduit hub
- Supplied with zinc plated screws
- UL467 Listed for the US and Canadian markets

- 4 AWG
- 3 AWG
- 2 AWG
- 1 AWG
- 1/0 AWG
- 2/0 AWG
- 3/0 AWG

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe EMT Size Range	2 1/2 in-4 in
Conductor - Pipe EMT Size	• 2 1/2 in • 3 in • 3 1/2 in • 4 in
Conductor - Armored Cable Size	N
Conductor - Copper Str Size Range	10 AWG - 3/0 AWG
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG

Dimensions

Dimension - Pad Width inch	2.44 in
Package Height	0.000 in
Dimension - Height mm	127.3 mm
Dimension - Height inch	5.01 in
Package Weight	0.000 lb.
Dimension - Width mm	29 mm
Dimension - Width inch	1.13 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	122 mm
Dimension - Length Overall inch	4.82 in

General

Plated	N
Material - Hardware	Zinc Plated Steel
UPC	781810142233
Material	Bronze Alloy
Plating Type	Unplated
UPC 12 Digit	781810142233
UPC 14 Digit GTIN	00781810142233

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1440
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)