



C4Y4/OL8D12G1SV Flexible Copper Braid

By Burndy
Catalog # C4Y4/OL8D12G1SV

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Certification - CSA Approved No
Standards - RoHS Compliance CM
Status

Dimensions

Dimension - L Length Overall	206 mm
mm	
Dimension - Length Overall	8.12 in
inch	
Width	2 in
Length	8.12 in

General

Material	Copper
UPC	621945467262

Logistics

Minimum Pack Quantity	10
Carton Quantity	10
Pallet Quantity	1440

Product Assets

[Catalog \[English\]](#)