



PLASTIC LASHING STRAP, 50 ft REEL

By Burndy
Catalog # C50PLLC

Lashing straps used in conjunction with CBPLLC buckles and spacers to secure communications cable to messenger strand. 250 lb tensile strength.

Features

- Loop strength 250 lbs.
- UV resistant and halogen free
- Use PSC2170130 strap tensioning tool for tensioning and cutting excess strap material

Application

For use on Messenger Cables;Also for use on Torque Tube

Dimensions

Weight	1.0 lb.
Height	0.875 in
Width	8.500 in
Length	50 foot reel / 600 in
Size	50 Foot Reel
Dimensions	50 foot reel / 600 in x 8.500 in x 0.875 in



General

UPC	096359657064
Material	Acetal

Logistics

Pallet Quantity	360
Carton Quantity	10

Operational

Operating Temperature Range	-40° C to +85° C
Celcius	

Product Assets

[Catalog \[English\]](#)