



C61, Cast Bronze Clamp, Cable to Water Pipe

By Burndy
Catalog # [C61](#)

Cast Bronze Clamp, Cable to Water Pipe, 6 AWG (Sol.), 1/2" - 1" Water Pipe

Features

- For grounding rigid conduit systems

Application

For Grounding Rigid Conduit Systems

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Pipe EMT Size	1/2 in 3/4 in 1 in
Conductor - Copper Str Size	8 AWG 7 AWG 6 AWG
Conductor - Copper Solid Size	10 AWG 9 AWG 8 AWG 7 AWG 6 AWG
Conductor - Armored Cable Size	N
Conductor - Copper Solid Size Range	10 AWG-6 AWG



Conductor Type	- Pipe EMT-Size - CU C Solid-Size
Conductor - Copper Str Size Range	8 AWG - 6 AWG

Dimensions

Dimension - Pad Width inch	1.06 in
Package Height	0.000 in
Dimension - Height mm	52.6 mm
Dimension - Height inch	2.07 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	59 mm
Dimension - Width mm	34 mm
Dimension - Width inch	1.34 in
Dimension - Length Overall inch	2.34 in

General

Material - Hardware Plated	Zinc Plated Steel
Sub Brand	N
UPC	C DIE
Type	781810142448
	WaterPipe Gounding Connectors
Material	Bronze Alloy
Plating Type	Zinc
UPC 12 Digit	781810142448
UPC 14 Digit GTIN	00781810142448

Logistics

Pallet Quantity	5000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)



A Hubbell brand