

C66, Cast Bronze Clamp, Cable to Water Pipe

By Burndy
Catalog # [C66](#)

Cast Bronze Clamp, Cable to Water Pipe, 6 AWG (Sol.), 1-1/4" - 2" Water Pipe



Features

- Cast bronze clamp for rigid conduit
- Supplied with zinc plated screws
- UL467 Listed for the US and Canadian markets

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG
Conductor - Pipe EMT Size Range	1 1/4 in-2 in
Conductor - Pipe EMT Size	• 1 1/4 in • 1 1/2 in • 2 in
Conductor - Armored Cable Size	N
Conductor - Copper Solid Size Range	10 AWG-6 AWG
Conductor Type	• Pipe EMT-Size • CU C Solid-Size

Conductor - Copper Str Size Range	8 AWG - 6 AWG
Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG

Dimensions

Dimension - Pad Width inch	1.40 in
Package Height	0.000 in
Dimension - Height mm	68.3 mm
Dimension - Height inch	2.69 in
Package Weight	0.000 lb.
Dimension - Width mm	34 mm
Dimension - Width inch	1.34 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	92 mm
Dimension - Length Overall inch	3.62 in

General

Plated	N
Material - Hardware	Zinc Plated Steel
UPC	781810142462
Material	Bronze Alloy
Plating Type	Zinc
UPC 12 Digit	781810142462
UPC 14 Digit GTIN	00781810142462

Logistics

Minimum Pack Quantity	20
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)