



CB2F12N Flexible Copper Covered Braid

By Burndy
Catalog # [CB2F12N](#)

Flexible Copper Covered Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance CM
Status

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Package Height	0.000 in
Length	12 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	781810454015
Material	Copper
UPC 12 Digit	781810454015
UPC 14 Digit GTIN	00781810454015

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1152
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)