



CB3G24N Flexible Copper Covered Braid

By Burndy
Catalog # [CB3G24N](#)

Flexible Copper Covered Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance NC
Status

Configuration

Connector Type Braid

Dimensions

Length	24 in
Dimension - L Length Overall mm	610 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	24.00 in
Thickness - Pad	0.69 in

General

Plated	N
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
UPC	781810451588
Material	Copper
UPC 12 Digit	781810451588
UPC 14 Digit GTIN	00781810451588

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)