



CBD24N Insulated Flex Tinned Cu Braid 24.00"x0.94"x0.13

By Burndy
Catalog # CBD24N

Insulated flexible tinned copper braid 24.00"x0.94"x0.13



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Dimensions

Length	24 in
Dimension - Width mm	24 mm
Dimension - Width inch	0.94
Dimension - L Length Overall mm	610
Height	0.13 in
Width	0.94 in
Dimension - Length Overall inch	24.00
Dimensions	24 in x 0.94 in x 0.13 in

General

Material - Ferrules	Copper
Physical Attribute - Number of Braids	1
UPC	781810544815
Material	Copper
UPC 12 Digit	781810544815
UPC 14 Digit GTIN	00781810544815

Logistics

Minimum Pack Quantity	30
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)