



CC22Y4/OL40D50G1 Braid Kit

By Burndy
Catalog # [CC22Y4/OL40D50G1](#)

Braid Kit



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Rope lay
----------------	----------

Current

Amperage Rating	1500 A
-----------------	--------

Dimensions

Package Height	0.000 in
Length	40.5 in
Package Weight	0.000 lb.
Dimension - Width inch	1.5 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	1029 mm
Weight	12.72 lb.
Height	0.68 in
Width	1.5 in
Dimension - Length Overall inch	40.5 in
Dimensions	40.5 in x 1.5 in x 0.68 in

General

UPC	621945449725
Material	Copper
UPC 12 Digit	621945449725
UPC 14 Digit GTIN	00621945449725

Logistics

Minimum Pack Quantity	1
Pallet Quantity	288
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)