



CC3Y4/OL17D50G4 Flexible Rope Lay Copper Braid

By Burndy
Catalog # [CC3Y4/OL17D50G4](#)

Flexible Rope Lay Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

Specifications

Certification - CSA Approved No

Configuration

Connector Type	Rope lay
Dimensions	
Dimension - L Length Overall mm	445 mm
Dimension - Length Overall inch	17.50 in
Length	17.5 in
General	
Material	Copper
UPC	621945468658
Logistics	
Minimum Pack Quantity	5
Carton Quantity	10
Pallet Quantity	960

Product Assets

[Catalog \[English\]](#)