



CCSC200900 Clear Cold Shrink, 9", .90"-1.28" Jacket OD Range

By Burndy
Catalog # [CCSC200900](#)

Clear Cold Shrink, Specially formulated silicone rubber offering excellent insulation and moisture resistant sealing for in-line cable connector systems. The rubber sleeves are factory expanded over a removeable, plastic ripcord housing. Installs quickly and easily with no heat gun or other installation tools. Passes TELCORDIA GR-347-CORE Abrasion and Cut Test up to 750 kcmil. Operating temperature range: -40°C to +105°C.

Application

Cold Shrink, Rated to 2000 Volts, offer insulation and moisture resistant sealing for in-line cable connector systems

General

Catalog Number	CCSC200900
Color	Clear
Connector Type	CLEAR
Material	Silicone Rubber
UPC	621945524255

Dimensions

Diameter	0.75 in
Dimension - Diameter Max before Shrink inch	2.09
Length	9.02 in
Width	0.12 in

Electrical Ratings

Voltage Rating	2000 V
----------------	--------



Certifications And Compliance

Certification - CSA Approved No

Logistics

Carton Quantity	250
Minimum Pack Quantity	1
Pallet Quantity	720

Product Assets

- [Brochures - STAY GROUNDED AND BONDED AT&T Ordering Guide](#)
- [Catalog Page - BURNDY Page D2 & D3 - Cold Shrink](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - Cable Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50090656](#)
- [Sell Sheets - Clear & Black Cold Shrink - Rated for 2000 Volts](#)
- [Specifications - CCSC200900](#)
- [Video - Grease Best PRACTICES](#)