



CCY10L18LT12G Covered Rope Lay Braid

By Burndy
Catalog # [CCY10L18LT12G](#)

Covered Rope Lay Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Rope lay
----------------	----------

Dimensions

Package Height	0.000 in
Length	18 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	476.50 mm
mm	
Dimension - Length Overall	18.76 in
inch	

General

UPC	781810674178
Material	Copper
UPC 12 Digit	781810674178
UPC 14 Digit GTIN	00781810674178

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)