



# CCY10L24LT12G Covered Rope Lay Braid

By Burndy  
Catalog # [CCY10L24LT12G](#)

Covered Rope Lay Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                              |    |
|------------------------------|----|
| Standards - RoHS Compliance  | CM |
| Status                       |    |
| Certification - CSA Approved | No |

## Configuration

|                              |                |
|------------------------------|----------------|
| Connector Type               | Rope lay       |
| <b>Dimensions</b>            |                |
| Length                       | 24 in          |
| Dimension - L Length Overall | 628.9 mm       |
| mm                           |                |
| Dimension - Length Overall   | 24.76 in       |
| inch                         |                |
| <b>General</b>               |                |
| UPC                          | 781810674185   |
| Material                     | Copper         |
| UPC 12 Digit                 | 781810674185   |
| UPC 14 Digit GTIN            | 00781810674185 |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

[Catalog \[English\]](#)