



CCY10L7G2 Rope Lay Braid

By Burndy
Catalog # [CCY10L7G2](#)

Rope Lay Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Rope lay
Dimensions	
Package Height	0.000 in
Length	7 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	190.5 mm
Dimension - Length Overall	7.50 in
General	
UPC	781810543597
Material	Copper
UPC 12 Digit	781810543597
UPC 14 Digit GTIN	00781810543597

Logistics

Minimum Pack Quantity	100
Pallet Quantity	12000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)