



CCY6CL10D60G1 Covered Rope Lay Braid

By Burndy
Catalog # [CCY6CL10D60G1](#)

Covered Rope Lay Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Rope lay
----------------	----------

Dimensions

Package Height	0.000 in
Length	10.6 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	284.98 mm
mm	
Weight	0.02 lb.
Dimension - Length Overall	11.22 in
inch	

General

UPC	781810670347
Material	Copper
UPC 12 Digit	781810670347
UPC 14 Digit GTIN	00781810670347

Logistics

Minimum Pack Quantity	500
Pallet Quantity	375
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)