



CCY6L18LT10B Covered Rope Lay Braid

By Burndy
Catalog # [CCY6L18LT10B](#)

Covered Rope Lay Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance UI
Status

Certification - CSA Approved No

Configuration

Connector Type Rope lay

Dimensions

Length 18 in

General

UPC	781810674659
Material	Copper
UPC 12 Digit	781810674659
UPC 14 Digit GTIN	00781810674659

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalog \[English\]](#)