



CFBGFR, Black Cover, Flame Retardant, for #8-6 AWG H-Tap

By Burndy
Catalog # [CFBGFR](#)

Black Cover only, for YH8C8C or YH6C6C, #8-6 AWG H-Taps
(connector not included)



Features

- Connector end stops
- Flexible fingers
- snap tight latches
- Hinged one piece construction

Application

Cover

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str	8 AWG-6 AWG
Compact Size	
Conductor - Max Length	0.65 in
Conductor - Material	COPPER
Wire Size	8 AWG-6 AWG
Conductor - AL Str Size	8 AWG-6 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	#8 AWG-#6 AWG
Range	
Conductor - Copper Str Size	8 AWG-6 AWG

Configuration

Connector Type	H-TAP COVERS BLACK
----------------	--------------------

Current

Voltage Rating	600 V
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Dimension - Height inch	1.16 in
Thickness	0.08 in
Package Weight	0.000 lb.
Dimension - Width inch	1.24 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	44 mm
mm	
Dimension - Length Overall	1.75 in
inch	

General

Color	Black
Plated	N
Color Code	Green
Trade Name	CRIMPIT™
Sub Brand	CRIMPIT
UPC	781810068830
Type	CF-FR, Flame Retardant
Insulation	Y
Material	POLYCARBONATE
Plating Type	Unplated
UPC 12 Digit	781810068830
UPC 14 Digit GTIN	00781810068830

Logistics

Pallet Quantity	14400
Carton Quantity	100

Operational

Temperature Rating	194
Operating Temperature	90 °C

Product Assets

[Catalog \[English\]](#)