



CH11C, Cable Tie Hanger, 100 pieces,
Natural

By Burndy
Catalog # CH11C

Nylon Cable Hanger

Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UV Rated	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Mounting Method	Screw
-----------------	-------

Dimensions

Package Height	1.750 in
Package Weight	0.320 lb.



Dimension - Width mm	13 mm
Dimension - Width inch	0.5
Package Length	13.250 in
Package Width	4.800 in
Dimension - Bundle Diameter	0.62
Max inch	

General

Color	Natural
Trade Name	UNIRAP™
UPC	781810336434
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810336434

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	36000
Carton Quantity	1000
Packaging Type	Bag

Product Assets

[Catalog \[English\]](#)