



CH12M0, Cable Tie Hanger, 1000 pieces, Black

By Burndy
Catalog # [CH12M0](#)

Nylon Cable Hanger



Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UV Rated	Yes
UL Listed	No
Certification - CSA Approved	No

Configuration

Mounting Method	Screw
-----------------	-------

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.
Dimension - Width mm	13 mm
Dimension - Width inch	0.50 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - Bundle Diameter	0.75
Max inch	

General

Color	Black
UPC	781810336502
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810336502

Logistics

Minimum Pack Quantity	3000
Pallet Quantity	1
Carton Quantity	1000
Packaging Type	Bag

Product Assets

[Catalog \[English\]](#)