



CH18C, Cable Tie Hanger, 100 pieces,
Natural

By Burndy
Catalog # [CH18C](#)

Nylon Cable Hanger

Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UV Rated	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Mounting Method	Screw
-----------------	-------

Dimensions

Package Height	2.500 in
----------------	----------

Package Weight	0.630 lb.
Dimension - Width mm	12 mm
Dimension - Width inch	0.47
Package Length	12.000 in
Package Width	10.000 in
Dimension - Bundle Diameter	1.33
Max inch	

General

Color	Natural
UPC	781810336632
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810336632

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	28000
Carton Quantity	1000
Packaging Type	Bag

Product Assets

[Catalog \[English\]](#)