



CH6M, Cable Tie Hanger, 1000 pieces, Natural

By Burndy
Catalog # CH6M

Nylon Cable Hanger



Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UV Rated	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Mounting Method	Screw
-----------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Dimension - Width mm	12 mm
Dimension - Width inch	0.47
Package Length	0.000 in
Package Width	0.000 in
Dimension - Bundle Diameter	.43
Max inch	

General

Color	Natural
Trade Name	UNIRAP™
UPC	781810336250
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810336250

Logistics

Minimum Pack Quantity	5000
Pallet Quantity	1
Carton Quantity	1000
Packaging Type	Bag

Product Assets

[Catalog \[English\]](#)