



CL501TNMHWSST, Cu Lay-in Lug, SS Mounting Hardware Included

By Burndy
Catalog # [CL501TNMHWSST](#)

Copper Lay-In Lug, Accommodates #14-4 AWG, #10 Stud, Tin Plated, with Stainless Steel Self Tapping Screw, Mounting Hardware Included

Features

- Open-faced design allows for fast lay-in of conductor without the need for cutting or breaking
- Stainless steel screws used for excellent corrosion resistance

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	14 AWG - 4 AWG
Range	

Dimensions

Package Height	1.480 in
Package Weight	0.694 lb.
Package Length	9.500 in
Package Width	9.300 in
Dimension - Hole Size inch	0.159 in

General

Plated	N
Trade Name	QIKLUG™
UPC	781810503454
UPC 12 Digit	781810503454
UPC 14 Digit GTIN	00781810503454

Logistics

Pallet Quantity	4800
Carton Quantity	50

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)