



CP2525, Heavy Duty Parallel Connector, Copper, A=1/0 Str, B=1/0 Str

By Burndy
Catalog # [CP2525](#)



Copper Alloy Heavy Duty Parallel Connector

Features

- High strength, high copper alloy
- Recommended for heavy duty parallel connections
- Silicon bronze hardware and cast copper body provides corrosion resistant assembly
- Long contact surface provides excellent full conductivity

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	1/0
Conductor - Copper Str Size B	1/0
Conductor - Copper Str Size A	1/0
Range	
Conductor - Copper Str Size B	1/0
Range	

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	13/16 in
Dimension - B Length fraction	3 in
Package Weight	0.000 lb.
Dimension - Width inch	1 9/16 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	3 in
Dimension - Width fraction	1-5/8 in

General

Plated	N
UPC	781810012833
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810012833
UPC 14 Digit GTIN	00781810012833

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)