



CP25A25A, Aluminum Alloy Connector for Tap or Parallel Connections

By Burndy
Catalog # [CP25A25A](#)



High strength, high conductivity aluminum body and hardware provide corrosion resistant assembly. Recommended for tap or parallel connections.

Features

- Cast Aluminum Parallel Groove Clamp with Aluminum Hardware
- Recommended for tap or parallel connections
- High strength, high conductivity
- Long contact surface for excellent contact and full conductivity
- PENETROX™ joint compound recommended for all combinations

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1/0 AWG
Conductor - Copper Str Size	1/0 AWG
Conductor - ACSR Str Size	1/0 (6/1) AWG
Range	
Conductor - ACSR Str Tap	1 AWG - 80 mm2
Range	

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	2.32 in
Package Weight	0.000 lb.
Dimension - Width inch	1.56 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	3.25 in

Force Related

Installation Torque	300 LBS/in
Recommended in-lb	

General

Plated	N
UPC	781810012956
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810012956
UPC 14 Digit GTIN	00781810012956

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)