



CP28A28A, Aluminum Alloy Connector for Tap or Parallel Connections

By Burndy
Catalog # [CP28A28A](#)



Aluminum Alloy Connector for tap or parallel connections

Features

- Cast Aluminum Parallel Groove Clamp with Aluminum Hardware
- Recommended for tap or parallel connections
- High strength, high conductivity
- Long contact surface for excellent contact and full conductivity
- PENETROX™ joint compound recommended for all combinations

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	4/0 AWG
Conductor - Copper Str Size A Range	4/0 AWG
Conductor - AL Str Size A	4/0 AWG
Conductor - AL Str Size B	4/0 AWG
Conductor - AL Str Size A Range	4/0 AWG
Conductor - AL Str Size B Range	4/0 AWG
Conductor - ACSR Str Size	134.6 (12/7) Leghorn kcmil
Conductor - Copper Str Size B Range	4/0 AWG
Conductor - ACSR Str Size Range	134.6 (12/7) Leghorn kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	73 mm
Dimension - Height inch	2.875 in
Dimension - Height fraction	2-7/8 in
Package Weight	0.000 lb.
Dimension - Width mm	54 mm
Dimension - Width inch	2.09 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	4 in
Dimension - Width fraction	2-1/8 in

Force Related

Installation Torque	300 LBS/in
Recommended in-lb	

General

Plated	N
UPC	781810012994
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810012994
UPC 14 Digit GTIN	00781810012994

Logistics

Minimum Pack Quantity	10
Pallet Quantity	360
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)