



CP2928, Heavy Duty Parallel Connector, Copper, A=250 kcmil, B=4/0 Str

By Burndy
Catalog # [CP2928](#)



Copper Alloy Heavy Duty Parallel Connector

Features

- High strength, high copper alloy
- Recommended for heavy duty parallel connections
- Silicon bronze hardware and cast copper body provides corrosion resistant assembly
- Long contact surface provides excellent full conductivity

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	0 mm
Dimension - Height inch	1 1/16 in
Package Weight	0.000 lb.
Dimension - Width inch	1 15/16 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	4 in

General

Plated	N
UPC	781810455838
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810455838
UPC 14 Digit GTIN	00781810455838

Product Assets

[Catalog \[English\]](#)