



CP29A29A, Aluminum Alloy Connector for Tap or Parallel Connections

By Burndy
Catalog # [CP29A29A](#)

High strength, high conductivity aluminum body and hardware provide corrosion resistant assembly. Recommended for tap or parallel connections

Features

- Cast Aluminum Parallel Groove Clamp with Aluminum Hardware
- Recommended for tap or parallel connections
- High strength, high conductivity
- Long contact surface for excellent contact and full conductivity
- PENETROX™ joint compound recommended for all combinations

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	250 kcmil
Conductor - Copper Str Size B	250 kcmil
Conductor - Copper Str Size A Range	250 kcmil
Conductor - AL Str Size A	• 250 kcmil • 266 kcmil
Conductor - AL Str Size B	• 250 kcmil • 266 kcmil
Conductor - AL Str Size A Range	250 kcmil-266 kcmil
Conductor - AL Str Size B Range	250 kcmil-266 kcmil
Conductor - ACSR Str Size	• 159 (12/7) Guinea kcmil • 176.9 (12/7) Dotterel kcmil • 190.8 (12/7) Dorking kcmil • 211.3 (12/7) Cochin kcmil • 203.2 (16/9) Brahma kcmil



Conductor - Copper Str Size B Range	250 kcmil
Conductor - ACSR Str Size Range	159 (12/7) Guinea kcmil-203.2 (16/9) Brahma kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	73 mm
Dimension - Height inch	2.875 in
Dimension - Height fraction	2-7/8 in
Package Weight	0.000 lb.
Dimension - Width inch	2.125 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	4 in
Dimension - Width fraction	2-1/8 in

Force Related

Installation Torque	300 LBS/in
Recommended in-lb	

General

Plated	N
UPC	781810013007
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810013007
UPC 14 Digit GTIN	00781810013007

Logistics

Minimum Pack Quantity	10
Pallet Quantity	1728
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)