



CP30A30A, Aluminum Alloy Connector for Tap or Parallel Connections

By Burndy
Catalog # CP30A30A



Aluminum Alloy Connector for tap or parallel connections

Features

- Cast Aluminum Parallel Groove Clamp with Aluminum Hardware
- Recommended for tap or parallel connections
- High strength, high conductivity
- Long contact surface for excellent contact and full conductivity
- PENETROX™ joint compound recommended for all combinations

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	300 kcmil
Conductor - Copper Str Size B	300 kcmil
Conductor - Copper Str Size A Range	300 kcmil
Conductor - AL Str Size A	300 kcmil
Conductor - AL Str Size B	300 kcmil
Conductor - AL Str Size A Range	300 kcmil
Conductor - AL Str Size B Range	300 kcmil
Conductor - ACSR Str Size	• 176.9 (12/7) Dotterel kcmil • 190.8 (12/7) Dorking kcmil • 211.3 (12/7) Cochin kcmil • 203.2 (16/9) Brahma kcmil • 266.8 (18/1) Waxwing kcmil • 266.8 (26/7) Owl kcmil • 266.8 (26/7) Partridge kcmil

Conductor - Copper Str Size B Range	300 kcmil
Conductor - ACSR Str Size Range	176.9 (12/7) Dotterel kcmil- 266.8 (26/7) Partridge kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	73 mm
Dimension - Height inch	2.875 in
Dimension - Height fraction	2-7/8 in
Dimension - B Length fraction	4-1/2 in
Package Weight	0.000 lb.
Dimension - Width inch	2.375 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	4.50 in
Dimension - Width fraction	2-3/8 in

Force Related

Installation Torque	300 LBS/in
Recommended in-lb	

General

Plated	N
UPC	781810012949
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810012949
UPC 14 Digit GTIN	00781810012949

Logistics

Minimum Pack Quantity	3
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)