



CP32A32A, Aluminum Alloy Connector for Tap or Parallel Connections

By Burndy
Catalog # [CP32A32A](#)



Aluminum Alloy Connector for tap or parallel connections

Features

- Cast Aluminum Parallel Groove Clamp with Aluminum Hardware
- Recommended for tap or parallel connections
- High strength, high conductivity
- Long contact surface for excellent contact and full conductivity
- PENETROX™ joint compound recommended for all combinations

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	400 kcmil
Conductor - Copper Str Size B	400 kcmil
Conductor - Copper Str Size A Range	400 kcmil
Conductor - AL Str Size A	• 397 kcmil • 400 kcmil
Conductor - AL Str Size B	• 397 kcmil • 400 kcmil
Conductor - AL Str Size A Range	397 kcmil-400 kcmil
Conductor - AL Str Size B Range	397 kcmil-400 kcmil
Conductor - ACSR Str Size	• 203.2 (16/9) Brahma kcmil • 266.8 (18/1) Waxwing kcmil • 266.8 (26/7) Owl kcmil • 266.8 (26/7) Partridge kcmil • 300.0 (26/7) Ostrich kcmil • 336.4 (18/1) Merlin kcmil • 336.4 (26/7) Linnet kcmil

Conductor - Copper Str Size B Range	• 336.4 (30/7) Oriole kcmil • 397.5 (18/1) Chickadee kcmil 400 kcmil
Conductor - ACSR Str Size Range	203.2 (16/9) Brahma kcmil-397.5 (18/1) Chickadee kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	76.2 mm
Dimension - Height inch	3 in
Dimension - Height fraction	3 in
Package Weight	0.000 lb.
Dimension - Width inch	2.50 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	5 in
Dimension - Width fraction	2-1/2 in

Force Related

Installation Torque	300 LBS/in
Recommended in-lb	

General

Plated	N
UPC	781810012987
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810012987
UPC 14 Digit GTIN	00781810012987

Logistics

Minimum Pack Quantity	5
Pallet Quantity	216
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)