



CP36A36A, Aluminum Alloy Connector for Tap or Parallel Connections

By Burndy
Catalog # [CP36A36A](#)



Aluminum Alloy Connector for tap or parallel connections

Features

- Cast Aluminum Parallel Groove Clamp with Aluminum Hardware
- Recommended for tap or parallel connections
- High strength, high conductivity
- Long contact surface for excellent contact and full conductivity
- PENETROX™ joint compound recommended for all combinations

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size Range	550 kcmil - 600 kcmil
Conductor - ACSR Str Size	477 kcmil

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall inch	5.25

Force Related

Installation Torque Recommended in-lb	300 LBS/in
---------------------------------------	------------

General

Plated	N
UPC	781810080986
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810080986
UPC 14 Digit GTIN	00781810080986

Logistics

Minimum Pack Quantity	6
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)