



CP37A37A, Aluminum Alloy Connector for Tap or Parallel Connections

By Burndy
Catalog # [CP37A37A](#)



Aluminum Alloy Connector for tap or parallel connections

Features

- Cast Aluminum Parallel Groove Clamp with Aluminum Hardware
- Recommended for tap or parallel connections
- High strength, high conductivity
- Long contact surface for excellent contact and full conductivity
- PENETROX™ joint compound recommended for all combinations

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	600 kcmil
Conductor - Copper Str Size B	600 kcmil
Conductor - Copper Str Size A Range	600 kcmil
Conductor - AL Str Size A	636 kcmil
Conductor - AL Str Size B	636 kcmil
Conductor - AL Str Size A Range	636 kcmil
Conductor - AL Str Size Range	636 kcmil
Conductor - AL Str Size B Range	636 kcmil
Conductor - ACSR Str Size	• 556.5 (24/7) Parakeet kcmil • 556.5 (26/7) Dove kcmil • 556.5 (30/7) Eagle kcmil • 605 (24/7) Peacock kcmil
Conductor - Copper Str Size B Range	600 kcmil

Conductor - ACSR Str Size Range	500 kcmil - 605 kcmil
---------------------------------	-----------------------

Dimensions

Package Height	0.000 in
Dimension - Height mm	85.7 mm
Dimension - Height inch	3.375 in
Dimension - Height fraction	3-3/8 in
Dimension - B Length fraction	5-1/4 in
Package Weight	0.000 lb.
Dimension - Width inch	3 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	5.25 in
Dimension - Length Overall inch	5.25

Force Related

Installation Torque Recommended in-lb	300 LBS/in
---------------------------------------	------------

General

Plated	N
UPC	781810012932
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810012932
UPC 14 Digit GTIN	00781810012932

Logistics

Minimum Pack Quantity	3
Pallet Quantity	700
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)