



Substation - Aluminum Parallel Groove Clamp

By Burndy
Catalog # CP3939L6

Cable Spacer



Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Tube Std Size	750 kcmil
----------------------------------	-----------

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall mm	203.2 mm
Dimension - Length Overall inch	8.00 in

Force Related

Installation Torque Recommended in-lb	480 lb-in
---------------------------------------	-----------

General

Plated	N
UPC	781810369074
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810369074
UPC 14 Digit GTIN	00781810369074

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)