



Substation - Aluminum Parallel Groove Clamp

By Burndy
Catalog # CP3R445A4

Parallel Cable Spacer -EHV



Features

- Rigid spacer for large range of cables
- Designed for short spacing with more contact control
- Two bolt design

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 1000 kcmil • 1033 kcmil • 1100 kcmil • 1113 kcmil
Physical Attribute - Number of Conductors Accommodated Total	3
Conductor - AL Str Size Range	1000 kcmil-1113 kcmil
Conductor Type	• AL C Str-Size • ACSR C Str-Size
Conductor - ACSR Str Size	• 900 (54/7) Canary kcmil • 954 (45/7) Rail kcmil • 954 (54/7) Cardinal kcmil • 1033.5 (45/7) Ortolan kcmil
Conductor - ACSR Str Size Range	900 (54/7) Canary kcmil-1033.5 (45/7) Ortolan kcmil

Configuration

Connector Type Spacer

Dimensions

Package Height	0.000 in
Dimension - Height mm	64.5 mm
Dimension - Height inch	2.54 in
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	248 mm
Dimension - B Length inch	3.00 in
Dimension - Length Overall inch	9.76 in

Force Related

Installation Torque Recommended in-lb	480 lb-in
---------------------------------------	-----------

General

Plated	N
Material - Hardware	Aluminum
UPC	781810491348
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810491348
UPC 14 Digit GTIN	00781810491348

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)