



CP4444, Heavy Duty Parallel Connector, Copper, A=1000 kcmil, B=1000 kcmil

By Burndy
Catalog # [CP4444](#)



Copper Alloy Heavy Duty Parallel Connector

Features

- High strength, high copper alloy
- Recommended for heavy duty parallel connections
- Silicon bronze hardware and cast copper body provides corrosion resistant assembly
- Long contact surface provides excellent full conductivity

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1000 kcmil
-------------------------	------------

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall inch	5

General

Plated	N
UPC	781810246689
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810246689
UPC 14 Digit GTIN	00781810246689

Logistics

Minimum Pack Quantity	4
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)