



Substation - Aluminum Parallel Groove Clamp

By Burndy
Catalog # [CP44AL6](#)

Cable Spacer



Features

- Rigid spacer for large range of cables
- Designed for short spacing with more contact control
- Two bolt design

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 900 kcmil • 954 kcmil • 1000 kcmil
Physical Attribute - Number of Conductors Accommodated Total	2
Conductor - AL Str Size Range	900 kcmil-1000 kcmil
Conductor - ACSR Str Size	• 874.5 (54/7) Crane kcmil • 900 (54/7) Canary kcmil • 954 (45/7) Rail kcmil • 954 (54/7) Cardinal kcmil
Conductor - ACSR Str Size Range	874.5 (54/7) Crane kcmil-954 (54/7) Cardinal kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	102 mm
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in

Force Related

Installation Torque Recommended in-lb	480 lb-in
---------------------------------------	-----------

General

Plated	N
Material - Hardware	Aluminum
UPC	781810270103
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810270103
UPC 14 Digit GTIN	00781810270103

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)