

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [CPR445A4](#)

Parallel Cable Spacer -EHV



Features

- Rigid spacer for large range of cables
- Designed for short spacing with more contact control
- One bolt design

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Physical Attribute - Number of Conductors Accommodated Total	2
Conductor - AL Str Size Range	1000 kcmil-1113 kcmil
Conductor - ACSR Str Size Range	900 (54/19) kcmil-1033.5 (45/7) kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	64.5 mm

Dimension - Height inch	2.54 in
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	146 mm
Dimension - B Length inch	3.00 in
Dimension - Length Overall inch	5.76 in

Force Related

Installation Torque Recommended in-lb	480 lb-in
---------------------------------------	-----------

General

Plated	N
Material - Hardware	Aluminum
UPC	781810493403
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810493403
UPC 14 Digit GTIN	00781810493403

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)