



CS3CI58220J, Medium Voltage Cold Shrink Termination Kit, 5-8kV 3-Phase Conversion Series-Indoor, Sleeve w/o Boot for Jacketed Concentric Conductor

By Burndy
Catalog # [CS3CI58220J](#)

Medium Voltage Cold Shrink Termination Kit, 5-8kV 3-Phase Conversion Series-Indoor, Sleeve w/o Boot for Jacketed Concentric Conductor

Features

- Rip and Grip does not require heat gun or any installation tools
- Spiral rip cord design provides for easy installation with effortless unwinding providing for fast removal of the hold-out core, Rip cord is recyclable
- All kits supplied with indoor cold shrinkable tube (unprinted), seal, cable tie, and installation guide
- Quick, easy, cost effective installation utilizing one-piece terminator design
- Test reports available upon request

Application

To be used with Single Conductor, 5-8 kV XPLE and EPR non-shielded power cables for the Electrical/Industrial/Construction market.

Specifications

Buy American Compliant	Under Review
Environmental Conditions	Indoor

Conductor

Conductor Range	• 5-8kV: #2 AWG-250 kcmil
-----------------	---



Configuration

Boot Type	NO
-----------	----

Current

Voltage Rating	5/8 kV
Phase	3-Phase

General

UPC	621945584990
Type	CS3CI58-J
Material	Silicone Rubber
Series	UD-JC Series

Logistics

Carton Quantity	3
-----------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)

- 15kV: #2-1 AWG