



CSB037800SR1, Cold Shrink Splice Kit,
Black, Conductor Range: #2-1/0 AWG

By Burndy
Catalog # [CSB037800SR1](#)

In-line splice sealing kit



Features

- Easy, safe installation
- Suitable for a wide range of cable sizes
- UV resistance, thermal stability
- No special tools or training required
- Forms a moisture proof seal
- Superior, time-saving insulation technology
- Indoor and outdoor applications

Application

Indoor and outdoor applications

Specifications

Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - CSA Approved	No

Conductor

Conductor Size	2AWG - 1/0AWG
----------------	---------------

Configuration

Connector Type	SEAL SPLICE KITS
----------------	------------------

Dimensions

Package Height	1.550 in
Dimension - Height mm	0 mm
Package Weight	1.108 lb.
Package Length	12.600 in
Package Width	9.050 in

General

Color	Black
Product Family	Wire/Cable/Hose Management & Accessories>Cold Shrink>Black Cold Shrink
Sub Brand	COLD SHRINK SPLICE
Product Type	Cold Shrink
UPC	621945441590
Type	CSB
Material	Rubber
UPC 14 Digit GTIN	00621945441590

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4500
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)