



CSB163900SR1, Cold Shrink Splice Kit, Black, Conductor Range: 1200-2000 kcmil

By Burndy
Catalog # [CSB163900SR1](#)

In-line splice sealing kit



Features

- Easy, safe installation
- Suitable for a wide range of cable sizes
- UV resistance, thermal stability
- No special tools or training required
- Forms a moisture proof seal
- Superior, time-saving insulation technology
- Indoor and outdoor applications

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor Size	1250kcmil - 2000kcmil
----------------	-----------------------

Configuration

Connector Type	SEAL SPLICE KITS
----------------	------------------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	621945442009
Material	Rubber
UPC 14 Digit GTIN	00621945442009

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	10

Product Assets

- [Catalog \[English\]](#)
[Catalog \[English\]](#)